

DID YOU KNOW?


about our... **DURASQUIRT® DTI WASHERS**




**NEW
PRODUCT**

DURASQUIRT® DTI WASHERS MECHANICAL GALVANISED ASTM F959M / CLASS 8.8


Part	Size	OD	ID	Thickness	Pack Qty
		min (mm)	min (mm)	min (mm)	
WDSTDGM12	M12	27.0	12.3	2.5	100
WDSTDGM16	M16	33.3	16.4	3.1	100
WDSTDGM20	M20	40.3	20.7	3.5	100
WDSTDGM24	M24	48.5	24.9	3.9	100
WDSTDGM30	M30	58.2	31.1	3.9	50
WDSTDGM36	M36	70.2	37.5	4.7	50



M12



M16



M20



The original Squirter® Washer has been replaced by the DuraSquirt® DTI Washer that features:

A durable squirt indication that lasts on the connection. Engineered to withstand the elements- wind, heavy rain and extreme temperatures. To prove how much DuraSquirt® DTI Washers can withstand, it was run through an automated dishwasher for 1 year. Despite the daily punishment of heated turbulent water and detergent, the squirt media was still visible.

Complete indication occurs after minimum tension has been achieved.

Simple to use and easy for installers and inspectors to see when the required tension is achieved. Not affected by poor torque tension correlation factors such as weathering, poor lubrication and damaged threads.


A clear visual indication when the bolt assembly is tensioned correctly by "squirting" bright orange indicator. By using DuraSquirt® DTI Washers the installer is alerted to poor quality AS1252 assemblies and other issues in the connection.

Independently tested from -50 to 104 degrees Celsius.


DID YOU KNOW?



about our... **DURASQUIRT® DTI WASHERS**



**NEW
PRODUCT**




M24

Bolting Completed in Three Easy Steps:

1. **Snug** – Steel plates in firm contact
2. **Squirt** – Drive it till it squirts!
No torque calibration or matchmarking required
3. **Inspect** – Visual indication of bolt tension; easy, safe and fast

Application:



Structural steel connections with **AS1252** - assemblies.



M30

Installation Check!

Tighten and ensure squirts are achieved for each bump, known as complete indication.



M36

